

# DMG

## EXPANDABLE MULTIMETERS

with graphic LCD

DMG 900 TOUCH SCREEN multimeter



IP65

Harmonic analysis and event logging

Ethernet interface

Function expandability using add-on modules

Transducer for remote measurement viewing

Measurement accuracy per EN 50470-3 (MID Class B)



**Lovato**  
**electric**

100% electricity

LOVATO ELECTRIC S.P.A.  
CONTROL SOLUTIONS  
FOR INDUSTRY

VIA DON E. MAZZA, 12  
24020 GORLE (BERGAMO) ITALY

Tel: +39 035 4282111  
Fax: +39 035 4282200  
E-mail: info@LovatoElectric.com

[www.LovatoElectric.com](http://www.LovatoElectric.com)



## Energy under control with maximum accuracy

- The backlit graphic display provides clear and intuitive viewing of the measurements.
- Parameter programming is available on 5-multilanguage menus.
- Expansion modules allow to configure the multimeter with respect to the application. The following expansion modules are available:
  - Ethernet, USB, RS232, RS485 and Profibus-DP interface
  - Multifunction digital and analog inputs
  - Static and relay outputs
  - Voltage and current analog outputs
  - Data storage with Energy Quality (EN 50160), clock calendar for events and data logging.